

## **Reference Material Certificate**

# 442/04

Aluminium Base (Type of Standard) AlSi, Set 440

## **Certified Values**

Element	Mass content [%]	Uncertainty [%]
Silicon (Si)	8.03	± 0.19
Iron (Fe)	0.73	± 0.03
Copper (Cu)	3.31	± 0.08
Manganese (Mn)	0.52	± 0.03
Magnesium (Mg)	0.142	± 0.006
Chromium (Cr)	0.030	± 0.003
Nickel (Ni)	0.045	± 0.003
Zinc (Zn)	1.04	± 0.05
Titanium (Ti)	0.121	± 0.005
Calcium (Ca)	0.0057	± 0.0005
Sodium (Na)	0.0017-0.0027	± 0.0004
Phosphorus (P)	(0.0020)	
Lead (Pb)	0.14	± 0.01
Tin (Sn)	0.141	± 0.007
Vanadium (V)	0.021	± 0.001
Zirconium (Zr)	0.058	± 0.003

The uncertainty reported is the result of standard deviation of all results multiplied with a factor of two and represents approximately the 95% confidence interval.

Values in brackets () are not certified but given for information only.

This certified reference material has elements with a range. Individually certified values for those elements are available on S-certificates only.

#### Manufacturing

This standard is produced using six strand hot top vertical continuous casting out of single melt.

### Homogeneity

Homogeneity testing is performed by means of spark emission spectroscopy. Tests involve making multiple measurements on individual samples taken at regular intervals along the entire length of each cast rod. Depending on the mass content of the element, the relative standard deviation of multiple measurements between discs or within one disc is typically found between 0.3% - 1% for alloying and other elements and 0.5% - 5% for trace elements.

## **Analysis**

The values listed in this analysis certificate are the results of multiple analyses performed in our chemical analysis laboratory which is an accredited test facility for aluminium alloys according to the international standard ISO 17025. The analyses are based on established wet chemical procedures.

# **Description of Sample**


This reference material is available in the form of discs (approx. Ø 60 x 25 mm).

# Intended use and Stability

This certified reference material is primarily intended for use in spark optical emission spectroscopy. Other applications are X-ray fluorescence spectrometry (XRF) and classical wet chemical procedures. The minimum sample size for wet chemical analysis is 0.2g. The material will remain stable for the period given below (certification validity) if it is stored in a dry and clean environment at room temperature.

#### **Instructions for Use**

Calibration measurements should be made within a ring between 2mm and 22mm from the edge of the CRM face. For wet chemical analysis chips have to be prepared by turning or milling of the sample surface.



Patrik Bachmann

Head of Inorganic Analytics

# **Traceability**

Traceability of the certified mass contents to the SI (Système International d'Unités) is ensured by calibration using certified standard solutions or pure metals or substances of known stoichiometry.

Dr. Benedikt Moser CTO

Suisse Technology Partners Ltd. Querstrasse 5 8212 Neuhausen am Rheinfall Switzerland

Phone: +41 52 551 11 00 Fax: +41 52 551 11 99 Email: refmat@suisse-tp.ch

Internet: https://reference-materials.ch

Date of certification: 22-Aug-2014
Certificate version 003: 04-Jan-2022
This certificate is valid until: Aug-2089