

Reference Material Certificate

613/08

Aluminium Base (Type of Standard)
AlMgSi, Set 610

Certified Values

Element	Mass content [%]	Uncertainty [%]
Silicon (Si)	0.413	± 0.011
Iron (Fe)	0.268	± 0.008
Copper (Cu)	0.0101	± 0.0005
Manganese (Mn)	0.0193	± 0.0007
Magnesium (Mg)	0.399	± 0.010
Chromium (Cr)	0.0050	± 0.0003
Nickel (Ni)	0.0044	± 0.0004
Zinc (Zn)	0.0087	± 0.0007
Titanium (Ti)	0.0146	± 0.0005
Arsenic (As)	0.0020	± 0.0004
Beryllium (Be)	0.0011	± 0.0001
Bismuth (Bi)	0.0036	± 0.0005
Calcium (Ca)	0.0005	± 0.0002
Cadmium (Cd)	0.0035	± 0.0002
Gallium (Ga)	0.0172	± 0.0009
Mercury (Hg)	0.0015	± 0.0004
Lithium (Li)	0.0006	± 0.0001
Sodium (Na)	0.0004	± 0.0002
Phosphorus (P)	0.0012	± 0.0003
Lead (Pb)	0.0107	± 0.0008
Antimony (Sb)	0.0085	± 0.0006
Tin (Sn)	0.0111	± 0.0007
Vanadium (V)	0.0109	± 0.0005
Zirconium (Zr)	0.0044	± 0.0004

The uncertainty reported is the result of standard deviation of all results multiplied with a factor of two and represents approximately the 95% confidence interval.

Manufacturing

This standard is produced using six strand hot top vertical continuous casting out of single melt.

Homogeneity

Homogeneity testing is performed by means of spark emission spectroscopy. Tests involve making multiple measurements on individual samples taken at regular intervals along the entire length of each cast rod. Depending on the mass content of the element, the relative standard deviation of multiple measurements between discs or within one disc is typically found between 0.3% - 1% for alloying and other elements and 0.5% - 5% for trace elements.

Analysis

The values listed in this analysis certificate are the results of multiple analyses performed in our chemical analysis laboratory which is an accredited test facility for aluminium alloys according to the international standard ISO 17025. The analyses are based on established wet chemical procedures.

Description of Sample


This reference material is available in the form of discs (approx. Ø 65 x 25 mm).

Intended use and Stability

This certified reference material is primarily intended for use in spark optical emission spectroscopy. Other applications are X-ray fluorescence spectrometry (XRF) and classical wet chemical procedures. The minimum sample size for wet chemical analysis is 0.2g. The material will remain stable for the period given below (certification validity) if it is stored in a dry and clean environment at room temperature.

Instructions for Use

Calibration measurements should be made within a ring between 2mm and 22mm from the edge of the CRM face. For wet chemical analysis chips have to be prepared by turning or milling of the sample surface.



Traceability

Traceability of the certified mass contents to the SI (Système International d'Unités) is ensured by calibration using certified standard solutions or pure metals or substances of known stoichiometry.

Dr. Benedikt Moser
CTO

Patrik Bachmann
Head of Inorganic Analytics

Suisse Technology Partners Ltd.
Querstrasse 5
8212 Neuhausen am Rheinfall
Switzerland

Phone: +41 52 551 11 00
Fax : +41 52 551 11 99
Email: refmat@suisse-tp.ch
Internet: <https://reference-materials.ch>

Date of certification: 12-Oct-2015
Certificate version 003: 04-Jan-2022
This certificate is valid until: Oct-2090