

Reference Material Certificate

423/03

Aluminium Base (Type of Standard)
AlSi, Set 420

Certified Values

Element	Mass content [%]	Uncertainty [%]
Silicon (Si)	11.2	± 0.3
Iron (Fe)	0.210	± 0.010
Copper (Cu)	0.0094	± 0.0006
Manganese (Mn)	0.062	± 0.004
Magnesium (Mg)	0.246	± 0.013
Chromium (Cr)	0.010	± 0.001
Nickel (Ni)	0.011	± 0.001
Zinc (Zn)	0.021	± 0.002
Titanium (Ti)	0.028	± 0.002
Calcium (Ca)	0.0009	± 0.0002
Cadmium (Cd)	0.0035	± 0.0003
Cobalt (Co)	0.220	± 0.012
Gallium (Ga)	0.0037	± 0.0003
Mercury (Hg)	0.0011	± 0.0003
Lithium (Li)	0.0002	± 0.0001
Sodium (Na)	0.0007	± 0.0003
Phosphorus (P)	0.0011	± 0.0003
Lead (Pb)	0.0013	± 0.0003
Antimony (Sb)	0.0097	± 0.0006
Tin (Sn)	0.0060	± 0.0003
Strontium (Sr)	0.0005	± 0.0002
Vanadium (V)	0.0117	± 0.0006
Zirconium (Zr)	0.0067	± 0.0005

The uncertainty reported is the result of standard deviation of all results multiplied with a factor of two and represents approximately the 95% confidence interval.

Manufacturing

This standard is produced using six strand hot top vertical continuous casting out of single melt.

Homogeneity

Homogeneity testing is performed by means of spark emission spectroscopy. Tests involve making multiple measurements on individual samples taken at regular intervals along the entire length of each cast rod. Depending on the mass content of the element, the relative standard deviation of multiple measurements between discs or within one disc is typically found between 0.3% - 1% for alloying and other elements and 0.5% - 5% for trace elements.

Analysis

The values listed in this analysis certificate are the results of multiple analyses performed in our chemical analysis laboratory which is an accredited test facility for aluminium alloys according to the international standard ISO 17025. The analyses are based on established wet chemical procedures.

Description of Sample


This reference material is available in the form of discs (approx. Ø 60 x 25 mm).

Intended use and Stability

This certified reference material is primarily intended for use in spark optical emission spectroscopy. Other applications are X-ray fluorescence spectrometry (XRF) and classical wet chemical procedures. The minimum sample size for wet chemical analysis is 0.2g. The material will remain stable for the period given below (certification validity) if it is stored in a dry and clean environment at room temperature.

Instructions for Use

Calibration measurements should be made within a ring between 2mm and 22mm from the edge of the CRM face. For wet chemical analysis chips have to be prepared by turning or milling of the sample surface.



Traceability

Traceability of the certified mass contents to the SI (Système International d'Unités) is ensured by calibration using certified standard solutions or pure metals or substances of known stoichiometry.

Dr. Benedikt Moser
CTO

Patrik Bachmann
Head of Inorganic Analytics

Suisse Technology Partners Ltd.
Querstrasse 5
8212 Neuhausen am Rheinfall
Switzerland

Phone: +41 52 551 11 00
Fax : +41 52 551 11 99
Email: refmat@suisse-tp.ch
Internet: <https://reference-materials.ch>

Date of certification: 14-Nov-2012
Certificate version 003: 04-Jan-2022
This certificate is valid until: Nov-2087